

Ordering Information:

A7921HE-2P - *** - ***
 1 2 3

1. Part NO.

2. Material:

(Blank): Nylon 66, UL94V-0



GWT: Nylon 66, UL94V-0, IEC 60335-1, 5th Edition
 Glow Wire Capable.

3. Color:

(Blank): White

BK: Black

IV: Ivory



SPECIFICATIONS:

Current Rating: 10A AC, DC

Voltage Rating: 250V AC, DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 10mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: 1500V AC/minute

Material: Nylon 66, UL94V-0



Unit	Scale	Sheet	TITLE		
mm	4:1	1 of 1	11.88mm PITCH HOUSING		
DRAWN	CHK'D	APPR			
Wenm Luo	Dlankul Wan	Jack Yin			
General Tolerances			THIRD ANGLE PROJECTION	DRAWING NO.	REV
x.xx±0.25				A7921HE-2P	A2
x.xxx±0.20					
x.xxxx±0.15					
ANGLES ±1°					

A2	CHANGE THE DRAWING	2022.01.13
A1	CHANGE THE DRAWING	2021.12.25
A0	NEW RELEASE	2009.05.10
REV	DESCRIPTION	DATE