


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2009.03.02	林澤云
02	△	變更圖號	2012.06.12	黃小燕

Specifications  
 Current Rating:2Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:500VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material:Phosphor Bronze  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T or the equivalent material  
 All materials must meet Greenconn requirement for environment protection.



### Ordering Information

C SFB204 - XX XX A 001 B 1 A X


No. of Pins per Row  
02~25

Standard Plating  
02=Gold Flash  
Selective Plating  
01=Tin  
05=Gold Flash/Tin

Color  
1=Black

Standard Packing  
C=Tube  
Selective Packing  
A=Box  
D=Tape&Reel

Recommended P.C.Board  
Layout  
(Tolerance:±0.05)



格菱股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE		DESIGN: 黃小燕	DATE: 2012.06.12
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2012.06.12
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2012.06.12
.XX*±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2012.06.12
.XXX*±1.0°	.XXX±0.10		

DWG. NO.	TITLE.
CSFB204-CA1BA	2.00 FEMALE HEADER SIDE ENTRY SERIES CONNECTOR
PART NO.	
CSFB204-XXXX A001B1AX	

REV.	UNIT.	SCALE.	PAGE.
02	mm	4:1	1/1