

1

2

3

4

5



6

7

8

9

| REV. | LOCAS. | DESCRIPTION | DATE | DRAWN |
|------|--------|-------------|------------|-------|
| 03 | △ | 變更料號 | 2009.03.03 | 李彬彬 |
| 04 | △ | 依上級要求變更圖號 | 2011.08.11 | 李芳忠 |



Specifications

Current Rating: 3Amp

Insulation Resistance: 1000MΩMin.

Dielectric Withstanding Voltage: 600VAC

Contact Resistance: 20mΩMax.

Operating Temperature: -40°C to +105°C

Materials

Contact Material: Phosphor Bronze

Insulator Material: Thermoplastic, UL 94V-0
PBT or the equivalent materialAll materials must meet Greenconn
requirement for environment protection.

△ Ordering Information △

C SHA101 - XX XX A 001 A X A X

No. Of Pins Per Row
02~40


Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black
6=Gray
K=Pink

Standard Packing
A=Box
Selective Packing
C=Tube
E=Cap+Tube
F=Cap+Tape&Reel

Recommended P.C.Board
Layout

(Tolerance: ±0.05)



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE

| | |
|------------|-----------|
| X.'±5.0' | X.±0.30 |
| .X'±3.0' | .X±0.25 |
| .XX'±2.0' | .XX±0.15 |
| .XXX'±1.0' | .XXX±0.10 |

| | | | |
|-----------|-------|-------|------------|
| DESIGN: | 李芳忠 | DATE: | 2011.08.11 |
| CHECKED: | 劉北平 | DATE: | 2011.08.11 |
| AUDITED: | 李輝 | DATE: | 2011.08.11 |
| APPROVED: | cc_li | DATE: | 2011.08.11 |

| | |
|----------|----------------------------|
| DWG. NO. | △△ CSHA101-CA1AA |
| PART NO. | △ CSHA101-XXXX A001AXAX |

TITLE.
2.54 FEMALE HEADER
SINGLE ROW DIP TYPE
CONNECTOR

| REV. | UNIT. | SCALE. | PAGE. | Symbol |
|------|-------|--------|-------|--------|
| 04 | mm | 4:1 | 1/1 | ☉ |

1

2

3

4

5

6

7

8

9