




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2010.06.15	馮代勇
02	△	變更新料號	2010.11.30	黃明霞




Specifications

Current Rating: 1Amp
 Insulation Resistance: 1000MΩ Min.
 Dielectric Withstanding: 300VAC
 Contact Resistance: 20mΩ Max.
 Operating Temperature: -40°C to +105°C


Materials

Contact Material: Phosphor Bronze
 Insulator Material: Polyester, UL 94V-0
 LCP or Equivalent Material.
 All materials must meet Greenconn requirement for environment protection

Ordering Information



RECOMMENDED P.C.B LAYOUT (Tolerance: ±0.05)



格稜股份有限公司
 Greenconn Corporation

GENERAL TOLERANCE	
X* ± 5°	X. ± 0.30
.X* ± 2°	.X ± 0.20
.XX* ± 1°	.XX ± 0.15
.XXX* ± 0.5°	.XXX ± 0.10

DESIGN: 黃明霞	DATE: 2010.11.30
CHECKED: 李新華	DATE: 2010.11.30
AUDITED: LEAR	DATE: 2010.11.30
APPROVED: LINK	DATE: 2010.11.30

DWG. NO. △ GPCA201-CA10CA
PART NO. GPCA201-XX XX A010C1AX

TITLE. 1.00 PIN HEADER DUAL ROWS DIP TYPE BASE 1.20H
--

REV. 02	UNIT. mm	SCALE. 1:1	PAGE. 1/1	⊕
---------	----------	------------	-----------	---