





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2021.04.22	郭康

Specifications
 Current Rating:1.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:300VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PEA126 - XX XX A 044 C 1 Z X

No. of Pins per Row 02~50
 Standard Plating 02=Gold Flash Selective Plating 01=Tin
 Color 1=Black
 Standard Packing A=Box Selective Packing C=Tube (04-50PIN)



3RD.ANG PROJ.
 PAGE. 1/1

GENERAL TOLERANCE	
X'±5.0'	X.±0.30
.X'±3.0'	.X±0.25
.XX'±2.0'	.XX±0.15
.XXX'±1.0'	.XXX±0.10

DESIGNED: 郭康 DATE: 2021.04.22
 CHECKED: DATE:
 APPROVED: DATE:

DWG. NO. GPEA126-CA44CZ
 PART NO. GPEA126-XXXX A044C1ZX

TITLE. 1.27 PIN HEADER BOARD SPACER SINGLE ROW DIP TYPE