





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2009.06.12	車 激
02	△	變更圖號	2011.05.20	曹 照
03	△	依業務求增加CAP配方	2011.12.05	李芳忠

Specifications  
 Current Rating:3Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:600VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material:Brass  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon6T(無鹵) or the equivalent material  
 All materials must meet Greenconn requirement for environment protection.



Recommended P.C.Board Layout  
 (Tolerance: ± 0.05)



### Ordering Information

G PHB201 - XX XX A 001 R 1 B X

No. of Pins per Row: 02~40  
 Standard Plating: 02=Gold Flash  
 Selective Plating: 01=Tin, 05=Gold Flash/Tin  
 Color: 1=Black  
 Standard Packing: A=Box  
 Selective Packing: C=Tube, E=Cap+Tube, F=Cap+Tape&Reel

格稜股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 李芳忠	DATE: 2011.12.05
CHECKED: 劉北平	DATE: 2011.12.05
AUDITED: 李輝	DATE: 2011.12.05
APPROVED: cc_li	DATE: 2011.12.05

DWG. NO.	△ GPHB201-CA1RB
PART NO.	GPHB201-XXXX A001R1BX

TITLE.	2.54 PIN HEADER DUAL ROWS R/A TYPE BASE 2.54H
--------	---

REV.	UNIT.	SCALE.	PAGE.
03	mm	3:1	1/1