




A B C D E F



N=PIN数



Material 材料
 Insulator 塑胶: PBT PA9T (UL 94V-0)
 Contact 端子: Brass 黄铜
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金
 Electrical Characteristics 电气特性
 Current rating 额定电流: 2.5Amps
 Dielectric Withstanding Voltage 耐压:
 AC 500V for 1 Minute.
 Insulator Resistance 绝缘电阻: 1000MΩ Min.
 Contact Resistance 接触电阻: 20mΩ Max.
 Operating Temperature 工作温度: -40°C ~ +105°C
 Max. Processing Temp 瞬时温度:
 240° C for 30-60 seconds
 (260° C for 10 seconds)



P.C.B LAYOUT

| | | | | | | | | |
|--------|-------|-----------|-------------------|----------------|---------------------------------------|----|----|----|
| 未注尺寸公差 | | | PZ2.54-2*NP | | 上海洲日电子有限公司 | | | |
| 公差 | | | | | Shanghai Zhouri Electronics CO.,LTD | | | |
| 尺寸 | 长度 | 角度 | 版本编号 20171018 A/O | | 上海康司玛电子设备进出口有限公司 | | | |
| X. | ±0.3 | ±5° | | | Shanghai KangSiMa Eletronic Equipment | | | |
| X.X | ±0.2 | ±3° | | | import and export Co.,LTD | | | |
| X.XX | ±0.15 | | | | TEL:86-21-34975176/51571121 | | | |
| 制图 | 周元金 | 201171018 | 图纸编号 | ZR20171018-257 | | | | |
| 审核 | 张海娜 | 201171018 | 物料编号 | | 1:1 | mm | 图幅 | A4 |
| 核准 | 章妹 | 201171018 | 第三视角 | | : 1 1 | | | |

A B C D E F