



name部位名称	unit 符号	specification 尺寸规格
No. of conductors导体数	pin	(N)P
margin width边距	M	0.5±0.08
Pitch间距	P	0.5±0.08
Total pitch总间距	SP	(N-1)×0.05±0.08
width总宽度	W	(N-1)×0.5±0.08
strip length 1端子长度1	S1	3±0.5
strip length 2端子长度2	S2	3±0.5
reinforeing tape length 1 补强板长度1	B1	4±2.0
reinforeing tape length 2 补强板长度2	B2	4±2.0
Total length产品长度	TL	(L)±2MM
Insulation length绝缘体长度	IL	(L-S1-S2)±2
Thickness insulation产品厚度	T	0.121±0.03
Cable thickness末端厚度	T1/T2	0.303±0.03
slanting切割斜度	A	< 0.3



型号: FC-0.5A-XXP-XXXMM

0.5: 0.5mm Pitch 间距

A: oppositedirectionge表示反向

NP: PIN位数

XXX:总长度

MM:单位

CAD FILE:			APPROVALS			DATE		DEALON 德之隆® ELECTRONICS CO.,LTD				
			DRAWN	G.M.Chen		2015/5/22		TITLE:	DC JACK			
			CHECKED					PART NO.	FC-0.5A-XXP-XXXMM			
			APPROVALS					UNIT: mm	SCALE: 1:1	SHEET 1 OF 1		
ECN NO.	REV.	DATE.	NEW DESCRIPTION.			CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	DRAWING NO.	PROJ:
	A							30~以上 ±0.30				
								10~30 ±0.20				
								5~10 ±0.15	±2'			
								~ 5 ±0.10				