



CAD FILE:

name部位名称	unit符号	specification尺寸规格
No. of conductors导体数	pin	(N)P
margin width边距	M	0.5±0.08
Pitch间距	P	0.5±0.08
Total pitch总间距	SP	(N-1)×0.05±0.08
width总宽度	W	(N-1)×0.5±0.08
strip length 1端子长度1	S1	3±0.5
strip length 2端子长度2	S2	3±0.5
reinforcing tape length 1补强板长度1	B1	4±2.0
reinforcing tape length 2补强板长度2	B2	4±2.0
Total length产品长度	TL	(L)±2MM
Insulation length绝缘体长度	IL	(L-S1-S2)±2
Thickness insulation产品厚度	T	0.121±0.03
Cable thickness末端厚度	T1/T2	0.303±0.03
slanting切割斜度	A	< 0.3



型号: FC-0.5B-XXP-XXXMM

0.5: 0.5mm Pitch 间距

B: oppositedirectione表示同向

NP: PIN位数

XXX:总长度

MM:单位

ECN NO.			REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE		DRAWING NO.	PROJ:
			A		NEW				30~以上 ±0.30	ANGLE		
									10~30 ±0.20		UNIT: mm	
									5~10 ±0.15	±2'	SCALE: 1:1	SHEET 1 OF 1
									~ 5 ±0.10			PROJ:

APPROVALS		DATE	
DRAWN	G.M.Chen	2015/5/22	
CHECKED			TITLE: DC JACK
APPROVALS			PART NO. FC-0.5B-XXP-XXXMM