



name部位名称	unit 符号	specification 尺寸规格
No. of conductors导体数	pin	(N)P
margin width边距	M	1.0±0.08
Pitch间距	P	1.0±0.08
Total pitch总间距	SP	(N-1)×0.1±0.08
width总宽度	W	(N-1)×1.0±0.08
strip length 1端子长度1	S1	4±0.5
strip length 2端子长度2	S2	4±0.5
reinforcing tape length 1 补强板长度1	B1	8±2.0
reinforcing tape length 2 补强板长度2	B2	8±2.0
Total length产品长度	TL	(L)±2MM
Insulation length绝缘体长度	IL	(L-S1-S2)±2
Thickness insulation产品厚度	T	0.121±0.03
Cable thickness末端厚度	T1/T2	0.303±0.03
slanting切割斜度	A	< 0.3



型号: FC-1.0A-XXP-XXXMM

1.0: 1.0mm Pitch 间距

A: oppositedirectionge表示反向

NP: PIN位数

XXX:总长度

MM:单位

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD		
DRAWN	G.M.Chen	2015/5/22	TITLE:	FPC软排线	
CHECKED			PART NO.	FC-1.0A-XXP-XXXMM	
APPROVALS			UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
TOLERANCES ARE		ANGLE	DRAWING NO.		PROJ:
30~以上	±0.30	±2'			
10~30	±0.20				
5~10	±0.15				
~ 5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			