



P.C.B LAYOUT

Specifications:
 规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:300V AC/minute
 耐受电压: 300V AC/分钟
 Temperature range:-40°C-+105°C
 温度范围: -40°C-+105°C
 Insulation resistance:≥500MΩ
 绝缘电阻: ≥500MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 Material:PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category:1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature:260±5°C, 10S
 回流焊温度: 260±5°C, 10S

X1322 W R S - 2xXX A - C40 D55 - E14 F06
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

1. Series No.
2. Category:W-Water
3. Welding Board Angle:R-Straight 90°
4. Welding Way:S-SMT
5. Row No -Pin No:2xXX-2x02P-2x50P
6. Special No: A-DIP and SMT
7. Pin length: C=4.0mm
8. Pin pitch:D=5.5mm
9. Pin length:E=1.4mm
10. Pin Length:F=0.6mm

X1322WRS-2xXXA-C40D55-E14F06	PA6T	Brass	X1322F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ生					ANGULAR ±5°
Δ数					L ≤ 4 ±0.2
Δ*					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN	VIEW:	PART NO.: X1322WRS-2xXXA-C40D55-E14F06
CHKD	UNIT: mm/in	DWG NO.: X-X1322WRS-2xXXA-C40D55-E14F06
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0