



PCB LAYOUT

Specifications:
 规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage: 300V AC/minute
 耐受电压: 300V AC/分钟
 Temperature range: -40°C~+105°C
 温度范围: -40°C~+105°C
 Insulation resistance: ≥500MΩ
 绝缘电阻: ≥500MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 Material: PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category: 1U"Gold
 镀层: 1U"Gold
 Reflow soldering temperature: 260±5°C, 10S
 回流焊温度: 260±5°C, 10S

X1321 W R S - 2xXX J - C40 D53
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Strighr 90°
4. Welding Way: S-SMT
5. Row No. Pin No: 2xXX-2x01~2x40Pin
6. Plastic Height: J=1.0mm
7. Pin Length: C=4.0mm
8. Pin Length: D=5.3mm

X1321WRS-2xXXJ-C40D53	PA6T	Brass	X1321F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN	VIEW:	PART NO.: X1321WRS-2xXXJ-C40D53
CHKD	UNIT: mm/in	DWG NO.: X-X1321WWR-2xXXJ-C40D53
APPD	SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	