


P.C.B LAYOUT



Specifications:

规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 2A AC/DC
 额定电流: 2A AC/DC
 Withstanding voltage: 500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range: -40°C ~ +105°C
 温度范围: -40°C ~ +105°C
 Insulation resistance: ≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 Material: PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category: 1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature: 255±5°C, 10S
 波峰焊温度: 255±5°C, 10S

X4611 W R - XX I U -C40 D50- E12 F12
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

1. Series No.
2. Category: W-Water
3. Welding Board Angle: R-Straight 90°
4. Row No -Pin No: XX-02P-40P
5. Plastic height: l=2.0mm
6. U: U-Type U
7. Plastic height: C=4.0mm
8. Pin Pitch: D=5.0mm
9. Pin length: E=1.25mm
10. Pin length: F=1.25mm

X4611WR-XXIU-C40D50-E12F12	PA6T	Brass	1U"Gold	X4611F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.00mm BTB Connector
DWN	VIEW:	PART NO.: X4611WR-XXIU-C40D50-E12F12
CHKD	UNIT: mm/in	DWG NO.: X-X4611WR-XXIU-C40D50-E12F12
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

DATE	日期
DESCRIPTION	文件工程章