



X4621WRS-2xXXI-C40D64



X4621WRS-2xXXIS-C40D64

Specifications:

规格:

- Voltage rating: 250V AC/DC
- 额定电压: 250V AC/DC
- Current rating: 2A AC/DC
- 额定电流: 2A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range: -40°C ~ +105°C
- 温度范围: -40°C ~ +105°C
- Insulation resistance: 1000M Ω min
- 绝缘电阻: 1000M Ω Min
- Contact resistance: 20M Ω Max
- 接触电阻: 20M Ω Max
- Plating Category: 1U" Gold
- 镀层: 1U" Gold
- Reflow soldering temperature: 260 \pm 5°C, 10S
- 回流焊温度: 260 \pm 5°C, 10S

X4621 W R S - 2xXX I S - C40 D64

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Welding Way: S-SMT
5. Row No. Pin No: 2xXX Pin
6. Plastic Height: I=2.0mm
7. Category: S-With positioning column
8. Pin length: C=4.0mm
9. Pin length: D=6.4mm

X4621WRS-2xXXI-C40D64	PA6T	Brass	X4621F
X4621WRS-2xXXIS-C40D64			
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND		SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN		VIEW:	PART NO.: X4621WRS-2xXXIS-C40D64
CHKD		UNIT: mm/in	DWG NO.: X-X4621WRS-2xXXIS-C40D64
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	$\pm 5^\circ$
$L \leq 4$	± 0.2
$4 < L \leq 16$	± 0.3
$16 < L \leq 63$	± 0.4
$L > 63$	± 0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED
文件	工程	章		