



X4621WRS-2xXXI-C40D64



X4621WRS-2xXXIS-C40D64

Specifications:

规格:

- Voltage rating: 250V AC/DC
- 额定电压: 250V AC/DC
- Current rating: 2A AC/DC
- 额定电流: 2A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range: -40°C - +105°C
- 温度范围: -40°C - +105°C
- Insulation resistance: 1000MΩ min
- 绝缘电阻: 1000MΩ Min
- Contact resistance: 20MΩ Max
- 接触电阻: 20MΩ Max
- Plating Category: 1U" Gold
- 镀层: 1U" Gold
- Reflow soldering temperature: 260 ± 5°C, 10S
- 回流焊温度: 260 ± 5°C, 10S

X4621 W R S - 2xXX I S - C40 D64

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Welding Way: S-SMT
5. Row No. Pin No: 2xXX Pin
6. Plastic Height: I=2.0mm
7. Category: S-With positioning column
8. Pin length: C=4.0mm
9. Pin length: D=6.4mm

X4621WRS-2xXXI-C40D64	PA6T	Brass	X4621F
X4621WRS-2xXXIS-C40D64			
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN	VIEW:	PART NO.: X4621WRS-2xXXIS-C40D64
CHKD	UNIT: mm/in	DWG NO.: X-X4621WRS-2xXXIS-C40D64
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED
Δ*				
Δx				
Δx				
文件工程章				