



Type R1

Type R2



PCB LAYOUT

Specifications:  
 规格:  
 Voltage rating: 250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating: 3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage: 1000V AC/minute  
 耐受电压: 1000V AC/分钟  
 Temperature range: -40°C +105°C  
 温度范围: -40°C +105°C  
 Insulation resistance: ≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance: ≤20mΩ  
 接触电阻: ≤20mΩ  
 Material: PA6T UL94V-0  
 材质: PA6T UL94V-0  
 Plating Category: 1U"Gold  
 镀层: 1U"Gold  
 Reflow soldering temperature: 260±5°C, 10S  
 回流焊温度: 260±5°C, 10S

X6512 W V S -XX H - C60 D48 - E100 X  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

1. Series No.
2. Category: W-Water
3. Welding Board Angle: V-Stright 180°
4. Welding Way: S-SMT
5. Row No -Pin No: XX-02P-40P
6. Plastic height: H=2.5mm
7. Pin length: C=6.0mm
8. Pin length: D=4.8mm
9. Pin length: E=10.0mm
10. Type: X-R1 ; R2

X6512WVS-XXH-C60D48-E100X	PA6T	Brass	1U"Gold	X6511F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

Δ修	日期
Δ改	日期
Δ效	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
					UNSPECIFIED TOLERANCES	



DSND	SCALE: N/A	MODEL TYPE: 2.54 BTB Connector
DWN	VIEW:	PART NO.: X6512WVS-XXH-C60D48-E100X
CHKD	UNIT: mm/in	DWG NO.: X-X6512WVS-XXH-C60D48-E100X
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED		SHEET 1/1
		REVISION A0