



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-40°C-+105°C
 温度范围: -40°C-+105°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 Material:PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category:1U"Gold
 镀层: 1U"Gold
 Rerlow soldering temperature:260±5°C, 10S
 回流焊温度: 260±5°C, 10S



P.C.B LAYOUT

X6521 W V S - 2xXX H S - C60 D75 X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- Series No.
- Category:W-Water
- Welding Board Angle:V-Straight 180°
- Welding Way S-SMT
- Row No -Pin No:2xXX-2x02P-2x40P
- Plastic Height:H=2.5mm
- Type:S-With positioning column
Blank-Without positioning column
- Pin length: C=6.0mm
- Pin Pitch:D=7.5mm
- TYPE:X-A:Fore and aft empty needle
B:Full

X6521WRS-2xXXHS-C60D75X	PA6T	Brass	1U"Gold	X6521F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ修					ANGULAR ±5°
Δ效					L ≤ 4 ±0.2
Δ效					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector
DWN	VIEW:	PART NO.: X6521WVS-2xXXHS-C60D75X
CHKD	UNIT: mm/in	DWG NO.: X-X6521WVS-2xXXHS-C60D75X
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED