


P.C.B LAYOUT



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-40°C+105°C
 温度范围: -40°C+105°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 Material:PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category:1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature:255±5°C, 10S
 波峰焊温度: 255±5°C, 10S

X6522 W R - 2xXX H - C60 D30 - E43 F03
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- Series No.
- Category:W-Water
- Welding Board Angle:R-Straight 90°
- Row No -Pin No:2xXX-2x02P-2x40P
- Plastic height: H=2.5mm
- Pin length: C=6.0mm
- Pin length:D=3.0mm
- Pin length:E=4.3mm
- Pin lengthF=0.3mm

X6522WR-2xXXH-C60D30-E43F03	PA6T	Brass	1U"Gold	X6521F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

Δ 姓	日期
Δ X	
Δ 数	
Δ X	

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
	REVISIONS				
					ANGLAR ±5°
					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector
DWN	VIEW:	PART NO.: X6522WR-2xXXH-C60D30-E43F06
CHKD	UNIT: mm/in	DWG NO.: X-X6522WR-2xXXH-C60D30-E43F06
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0