

RoHS

MATERIAL LIST

TEL:0769-82001899

VER

DESCRIBE

NATE

DRAWN

A0

新图框编制

2020/08/29

姜光鸿

NO.	PART	MATERIAL	COATING/COLOR	QTY
1	HOUSING	PBT UL94V-0	BLACK	1
2	TERMINALS	BRASS	PLATING GOLD	N

NOTE:

1 TECHNICAL PARAMETER:

1.1 RATINGS: 3A/250V (DC AC)





1.2 CONTACT RESISTANCE: 20MΩ MAX.

1.3 INSULATION RESISTANCE: 1000MΩ MIN

1.4 WITHSTAND VOLTAGE: 600V AC/MINUTE

1.5 WORKING TEMPERATURE: -40°C TO +105°C

料号释义:								
EH	254	V	12	XX	X	X	X	
EH=牛角	127=1.27间距 100=1.00间距 200=2.00间距 254=2.54间距	焊板角度: V:直插 R:弯插 VS:立贴 RS:卧贴	产品类型: 12=单塑双排	XX=Pin位	耳朵区分: routine=A A=长耳 B=短耳	材质: routine=PBT P=PBT 6=PA6T 9=PA9T L=LCP	镀层: routine=G/F 0=G/F 2=Au2U* 3=Au3U* 5=Au5U*	



PIN	Dimensions(mm)	
	A	B
06	5.08	26.82
08	7.62	29.36
10	10.16	31.90
14	15.24	36.98
16	17.78	39.52
18	20.32	42.06
20	22.86	44.80
24	27.94	49.68
26	30.48	52.22
30	35.56	57.30
34	40.64	62.38
40	48.26	70.00
50	60.96	82.70
60	73.66	95.40
64	78.74	100.48

TOLERANCE UNLESS OTHERWISE

UNIT

mm

XFCN 兴飞连接器有限公司  
XFCN CONNECTORS CO., LTD.

DRAWN

姜光鸿

X. ±0.30

X° ±5°

.X ±0.20

.X° ±2°


.XX ±0.08

.XX° ±1°

.XXX ±0.03

.XXX° ±0.5°

VIEW



SCALE

1:1

TYPE

2.54mm pin horn connector

NUMBER

XF-EH001

PART.NO.

EH254V-12-XXP

CHKD

APPD

DATE

2020/08/29