


面板底部开孔
 Open hole at bottom of panel

技术参数:

- 插芯:
- 插针数: 10
 - 额定电流: 30A
 - 额定电压: 500V
 - 额定脉冲电压: 6kV
 - 污染等级: 3
 - 依据UL/CSA的额定电压: -
 - 绝缘阻抗: $>10^{10}\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500
- 插针:
- 接线方式: 螺钉连接
 - 材料: 铜合金
 - 表面处理:
 - 镀银
 - 接触电阻: $\leq 3\text{m}\Omega$
 - 线径范围: $0.32-4.0\text{mm}^2(22-12 \text{ AWG})$
 - 剥线长度: -
 - 工具:
 - 冷压钳: -
 - 退针器: -

Technical specification:

- Inserts:
- No. of contact: 10
 - Rated current: 30A
 - Rated voltage: 500V
 - Rated impulse voltage: 6kV
 - Pollution degree: 3
 - Rated voltage acc.to UL/CSA: -
 - Insulation resistance: $>10^{10}\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500
- Contacts:
- Terminal: screw terminal
 - Material: copper alloy
 - Surface:
 - hard-gold plated
 - Contact resistance: $\leq 3\text{m}\Omega$
 - Wire gauge: $0.32-4.0\text{mm}^2(22-12 \text{ AWG})$
 - Stripping length: -
 - Tools:
 - Crimp contact tool: -
 - Contact removal tool: -



					表面处理 Finish	-				图号 Drawing No.	-		
					材料 Material	-				产品代号 Part Code	HCC-010-M		
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date					产品料号 Part No.	1330100110001	
姓名/Name	日期/Date	姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.					产品名称 Part Name	-
绘图 Drawn	WL KANG	27.02.2017	标准化 Stand.	-	-								
审核 Checked	ZW WU	27.02.2017											
工艺 Process	-	-	批准 Approved	YY LUO	27.02.2017	All Dimensions in mm Original Size DIN A 4						厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD	