



REV	LOCAS	DESCRIPTION	DRAW	DATE
AO	NEW	PERLIMINARY	Wang	2014.04.15



- NOTES:
- MATERIAL:
    - Housing: High Temperature Thermoplastic UL94V-0, Color: Black
    - Terminal: Copper Alloy
    - Shell: Stainless Steel
  - SPECIALITY:
    - Rated Current: 0.5A
    - Rated Voltage: 30V
    - Contact Resistance: 50mΩ Max
    - Insulation Resistance: 100MΩ Min 100V DC
    - Dielectric Withstanding Voltage: 100V AC
    - Solder Ability: 245±5°C; 5±0.5s
    - Durability: 5000 cycles
    - Operating Condition: Temperature: -30°C~+80°C; Humidity: 80%R.H Max

Card PIN No.	PIN NAME	SIM PIN No.
PIN 1	VCC	PIN 1
PIN 2	RST	PIN 2
PIN 3	CLK	PIN 3
PIN 4	RESERVED	
PIN 5	GND	PIN 5
PIN 6	VPP	PIN 6
PIN 7	I/O	PIN 7
PIN 8	RESERVED	

Ordering Information



MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)			<b>DongGuan D-CHAIN Precision Components CO, Ltd</b>	
	DESIGN	Wang	DATE	2014.04.15
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3'	CHECKED	Andy.L	DATE	2014.04.15
	APPROVED	Andy.L	DATE	2014.04.15
	TITLE: 3.0H 6PIN SIM CARD			
PART No.	SA0602254300-044-01			REV: AO
DRAWING No.	DQSA0602254300-044-01			SCALE: 1:1
				UNIT: mm
				SHEET: 1/1