



REV	LOCS	DESCRIPTION	DRWN	DATE
01	NEW	PERIMINARY	LITAO	2015.11.24



- NOTES:
- MATERIAL:
 - Housing: LCP+30% Glass Filled UL94V-0; Color Black.
 - Contact: Phosphor Bronze; T=0.12mm.
 - Shell: Stainless Steel; T=0.15mm.
 - FINISH:
 - Contact: Plated Gold Flash on the Contact Area and Solder Tails: Underplated Nickel Over all
 - Shell: Plated Gold on the Solder Tails, Underplated Nickel Over all
 - SPECIALTY:
 - Rated current: 0.5A
 - Rated voltage: 50V
 - Contact Resistance: 80mΩ MAX
 - Insulation Resistance: 100MΩ MIN
 - Dielectric withstanding voltage: 100V AC.
 - Solder ability: 245±5°C, 5±0.5s.
 - Operating condition: temperature: -30°C~+80°C Humidity: 80% R.H MAX

Ordering Information

S A 12 01 080 275- 94

S:SIM Card Series

A:Finished Product

No. of PINS: 12(12PIN)

Plating Number: _____

Running Number

275:Height 2.75mm

080:Pitch 0.80mm

PN NO	PN No.
P1-A/B	VCC : PWM SIGNAL AND GND
P2-A/B	RST : RESET SIGNAL
P3-A/B	CLK : CLOCKING SIGNAL
P4-A/B	GND : PWM SIGNAL AND GND
P5-A/B	VPP : PROGRAMMING VOLTAGE
P6-A/B	I/O : SERIAL DATA INPUT/OUTPUT

MEASURE POINT:	
QUADRANT POINT	(QP)
TANGENCY POINT	(TP)
INTERSECTION POINT	(IP)
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	
X	±0.30
Xx	±0.20
Xxx	±0.15
ANGULAR	±5

DESIGN		LITAO		DATE		2015.11.24		TITLE:	
CHECKED	DATE	DATE	DATE	DATE	DATE	DATE	DATE	DATE	2.75H DOUBLE MICRO SIM CARD
APPROVED	DATE	DATE	DATE	DATE	DATE	DATE	DATE	DATE	INSERT 1.10 TYPE
PART No.	SA1201080275-94	REV:	01	SCALE:	1:1	UNIT:	mm	SIZE:	A4
DRAWING No.	00541201080275-94	SIZE:	A4	SHEET:	1/1	UNIT:	mm		

D-CHAIN

SHEN ZHEN D-CHAIN TECHNOLOGY CO.,LTD