


日期/Date
 档案员
 Filing Clerk




技术参数:

- 插芯:
- 插针数: 3
 - 额定电流: 40A
 - 额定电压: 690V
 - 额定脉冲电压: 8kV
 - 污染等级: 3
 - 依据UL的额定电压: 600V
 - 绝缘阻抗: $>10^{10}\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500
- 插针:
- 接线方式: 轴向螺栓连接
 - 材料: 铜合金
 - 表面处理: 镀银
 - 接触电阻: $<1\text{m}\Omega$
 - 线径范围: $2.5-8\text{mm}^2$
 - 内六角扳手: SW-2*40
 - 剥线长度:
 - mm^2 : 2.5 4 6 10
 - mm : 5^{+1} 5^{+1} 8^{+1} 11^{+1}
 - 拧紧力矩:
 - mm^2 : 2.5 4 6 10
 - $\text{N}\cdot\text{m}$: 1.5 1.5 2 2

Technical specification:

- Inserts:
- No. of contact: 3
 - Rated current: 40A
 - Rated voltage: 690V
 - Rated impulse voltage: 8kV
 - Pollution degree: 3
 - Rated voltage acc.to UL: 600V
 - Insulation resistance: $>10^{10}\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500
- Contacts:
- Terminal: axial screw terminal
 - Material: copper alloy
 - Surface: hard-silver plated
 - Contact resistance: $<1\text{m}\Omega$
 - Wire gauge: $6-10\text{mm}^2$
 - Hexagonal driver: SW-2*40
 - Stripping length:
 - mm^2 : 2.5 4 6 10
 - mm : 5^{+1} 5^{+1} 8^{+1} 11^{+1}
 - Tightening torque:
 - mm^2 : 2.5 4 6 10
 - $\text{N}\cdot\text{m}$: 1.5 1.5 2 2



| | | | | | | | | | | | |
|---------------|--------------|------------------|----------------|---------|-----------------|----------------|------------|---|------------|---|------------------|
| | | | | | | 表面处理 Finish | - | | | 图号 Drawing No. | - |
| | | | | | | 材料 Material | - | | | 产品代号 Part Code | HMK-003.1-M |
| 标记 Mark | 处数 Number | 变更描述/Description | | | 签名 Signature | | 日期 Date | - | | | 产品料号 Part No. |
| | 姓名/Name | 日期/Date | | 姓名/Name | 日期/Date | 比例 Scale | 版本 REV. | 重量 Weight | 数量 Qty. | 产品名称 Part Name | - |
| 绘图 Drawn | BQ LUO | 18.10.2010 | 标准化 Stand. | - | - | 1:1 | V1.0 | 30.5g | - | | |
| 审核 Checked | P RAO | 18.10.2010 | | | | | | | | | |
| 工艺 Process | - | - | 批准 Approved | YY LIN | 18.10.2010 | | | All Dimensions in mm Original Size DIN A 4 | | 厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD | |