



技术参数:

插芯:

- 插针数: 2x4
- 额定电流: 10A
- 额定电压: 50V
- 额定脉冲电压: 0.8kV
- 污染等级: 3
- 绝缘阻抗:  $>10^{10}\Omega$
- 材料: 锌合金(钝化), 聚碳酸酯
- 颜色: RAL 7032(浅灰色)
- 温度范围:  $-40^{\circ}\text{C} - +85^{\circ}\text{C}$
- 依据UL 94的阻燃等级: V0
- 可插拔次数:  $>500$

插针:

- 接线方式: 冷压连接
- 材料: 铜合金
- 表面处理:
  - 镀银
  - 镀金
- 接触电阻:  $<3\text{m}\Omega$
- 线径范围:  $0.14-2.5\text{mm}^2(26-14\text{ AWG})$
- 剥线长度: 8mm
- 工具:
  - 冷压钳: TL02G
  - 退针器: TL00

Technical specification:

Insters:

- No. of contact: 2x4
- Rated current: 10A
- Rated voltage: 50V
- Rated impulse voltage: 0.8kV
- Pollution degree: 3
- Insulation resistance:  $>10^{10}\Omega$
- Material: zinc die-cast(passivating treatment), polycarbonate
- Colour: RAL 7032(light grey)
- Temperature range:  $-40^{\circ}\text{C} - +85^{\circ}\text{C}$
- Flammability acc.to UL 94: V0
- Mating cycles:  $>500$

Contacts:

- Terminal: crimp terminal
- Material: copper alloy
- Surface:
  - hard-gold plated
  - hard-silver plated
- Contact resistance:  $<3\text{m}\Omega$
- Wire gauge:  $0.14-2.5\text{mm}^2(26-14\text{ AWG})$
- Stripping length: 8mm
- Tools:
  - Crimp contact tool: TL02G
  - Contact removal tool: TL00

						表面处理 Finish	-		图号 Drawing No.	-
						材料 Material	-		产品代号 Part Code	HMMB-008-MC
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date			产品料号 Part No.	1290080100503
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name
绘图 Drawn	CY WU	27.02.2017	标准化 Stand.	-	-	1:1	V1.1	44.5g	-	-
审核 Checked	ZW WU	27.02.2017								
工艺 Process	-	-	批准 Approved	YY LOU	27.02.2017	All Dimensions in mm Original Size DIN A 4		厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD		