


REV	LOCAS	DESCRIPTION	DRAW	DATE
01	NEW	INITIAL RELEASE	Junly	2010.08.16
05	△05	ECN20120040	Huang	2012.09.26
06	△06	ADD LOGO	Wang	2014.03.17

NOTES:

- MATERIAL:
 - Housing:High Temperature Thermoplastic UL94V-0; Color Black.
 - Terminal:Copper Alloy.
 - Nail:Stainless Steel
- SPECIALITY:
 - Rated current:2.0A
 - Rated voltage:30V
 - Contact Resistance:50mΩ MAX
 - Insulation Resistance:100MΩ MIN 100V DC
 - Dielectric withstanding voltage: 100V AC.
 - Solder ability:245±5℃, 5±0.5s.
 - Durability:5000 Cycles Min.
 - Operating condition:Temperature: -30℃~+80℃;

Ordering Information Humidity: 80% R.H MAX



PART No.	DIM A	DIM B	PART No.	DIM A	DIM B
BA0307300450-26	4.50	3.00	BA0307300600-26	6.00	4.50
BA0307300500-26	5.00	3.50	BA0307300620-26	6.20	4.70
BA0307300550-26	5.50	4.00			

QUADRANT POINT (QP)	SHEN ZHEN D-CHAIN TECHNOLOGY CO.,LTD					
TANGENCY POINT (TP)						
INTERSECTION POINT (IP)						
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESING	Huang	DATE	2012.09.26	TITLE:	
X. ±0.25	CHECKED	Andy.L	DATE	2012.09.26	3PIN BATTERY PH:3.00mm SMT TYPE WITH 2 POST	
X.x ±0.20	APPROVED	Andy.L	DATE	2012.09.26		
X.xx ±0.15	PART NO: BA0307300XXX-26			REV: 06	SCALE: 5:1	UNIT: mm
ANGULAR ±3'	DRAWING NO: DQBA0307300450-26			SIZE: A4	SHEET: 1/1	

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05