


技术参数:

- 插芯:
- 插针数: 2x4
  - 额定电流: 10A
  - 额定电压: 50V
  - 额定脉冲电压: 0.8kV
  - 污染等级: 3
  - 绝缘阻抗:  $\geq 10^{10}\Omega$
  - 材料: 锌合金 (钝化), 聚碳酸酯
  - 颜色: RAL 7032 (浅灰色)
  - 温度范围:  $-40^{\circ}\text{C} - +85^{\circ}\text{C}$
  - 依据UL 94的阻燃等级: V0
  - 可插拔次数:  $\geq 500$
  - 不与框架屏蔽导电
- 插针:
- 接线方式: 冷压连接
  - 材料: 铜合金
  - 表面处理:
    - 镀银
    - 镀金
  - 接触电阻:  $\leq 3\text{m}\Omega$
  - 线径范围:  $0.14-2.5\text{mm}^2(26-14 \text{ AWG})$
  - 剥线长度: 8mm
  - 工具:
    - 冷压钳: TL02G
    - 退针器: TL00

Technical specification:

- Insters:
- No. of contact: 2x4
  - Rated current: 10A
  - Rated voltage: 50V
  - Rated impulse voltage: 0.8kV
  - Pollution degree: 3
  - Insulation resistance:  $\geq 10^{10}\Omega$
  - Material: zinc die-cast(passivating treatment), polycarbonate
  - Colour: RAL 7032(light grey)
  - Temperature range:  $-40^{\circ}\text{C} - +85^{\circ}\text{C}$
  - Flammability acc.to UL 94: V0
  - Mating cycles:  $\geq 500$
  - Do not conduct with the frame shield
- Contacts:
- Terminal: crimp terminal
  - Material: copper alloy
  - Surface:
    - hard-gold plated
    - hard-silver plated
  - Contact resistance:  $\leq 3\text{m}\Omega$
  - Wire gauge:  $0.14-2.5\text{mm}^2(26-14 \text{ AWG})$
  - Stripping length: 8mm
  - Tools:
    - Crimp contact tool: TL02G
    - Contact removal tool: TL00



						表面处理 Finish	-			图号 Drawing No.	-
						材料 Material	-			产品代号 Part Code	HMMB-008-MC 3SP
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date				产品料号 Part No.	1290080100508
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name	-
绘图 Drawn	CY WU	27.02.2017	标准化 Stand.	-	-	1:1	V1.1	44.5g	-		
审核 Checked	ZW WU	27.02.2017									
工艺 Process	-	-	批准 Approved	YY LOU	27.02.2017			All Dimensions in mm Original Size DIN A 4		厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD	