



材料Material
 原料Insulator:PBT,(UL 94V-0)
 相关材料Related Material: Brass
 表面涂层Surface Coating:Over Nickel

规格Specification
 额定电流Current rating:1.5AMP
 耐压Dielectric Withstanding Voltage:1000v Ac Min
 绝缘电阻Insulation Resistance:1000MΩ min
 接触电阻Contact resistance:30MΩ Max
 工作温度Operating Temperature:-45℃~+105℃

1	Dimension (mm)	
	A	B
6	5.08	12.32
8	7.62	14.86
10	10.16	17.40
12	12.70	19.94
14	15.24	22.48
16	17.78	25.02
20	22.86	30.10
24	27.94	35.18
26	30.48	37.72
30	35.56	42.80
34	40.64	47.88
40	48.26	55.50
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD	
		上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Electronic Equipment import and export Co.,LTD	
绘图: MAXIA	日期: 20170320	tel:021-51571121	http://www.zhouri.net
审核: FANHUA	日期: 20170320	fax:021-51571120	http://www.ksmchian.com
版本编号: ZRLCGY2015-05-01-CJ	产品名称: FC-2.54-*P		
第三视角:	单位: mm	比例:	图幅:A4 页次 共 01 第 01