



P.C.B LAYOUT

Material材料  
 Insulator 塑胶: 30%Glass filled PBT, (UL 94V-0)  
 Contact 端子: Brass 黄铜  
 Electrical Characteristics 电气特性  
 Current rating 额定电流: 1.5AMP  
 Dielectric Withstanding Voltage 耐压:  
 AC 1000V for 1Minute.  
 Insulator Resistance 绝缘电阻:  
 1000MΩ Min. AT DC 500V.  
 Contact Resistance 接触电阻: 30MΩ Max. AT DC 100mA.  
 Operating Temperature 工作温度: -40℃~+105℃

未注公差尺寸			KSM-9001-17481C 348		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD				
公差					上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD				
尺寸	长度	角度	版本号	20171018 A/0		TEL:86-21-34975176/51571121			
X.	±0.3	±5°							
X.X	±0.2	±3°							
X.XX	±0.15		图编号	ZR20171018-22					
绘图	周元金	201171018	物料编号	110667					
审核	张海娜	201171018			1:1		mm 图幅		A4
核准	章妹	20181113					: 1 1		