


P.C.B LAYOUT

Material材料
 Insulator塑胶:30%Glass filled PBT, (UL 94V-0)
 Contact 端子: Brass黄铜
 Electrical Characteristics电气特性
 Current rating额定电流:1.5AMP
 Dielectric Withstanding Voltage耐压:
 AC 1000V for 1Minute.
 Insulator Resistance绝缘电阻:
 1000MΩ Min. AT DC 500V.
 Contact Resistance接触电阻:30MΩ Max. AT DC 100mA.
 Operating Temperature工作温度:-40℃~+105℃

未注公差尺寸			KSM-9001-35321C		上海洲日电子有限公司		
公差			232		Shanghai Zhouri Electronics CO.,LTD		
尺寸	长度	角度	版本号		20171018 A/0		
X.	±0.3	±5°					
X.X	±0.2	±3°					
X.XX	±0.15		图编号		ZR20171018-7		
绘图	周元金	201171018	物料编号		110653		
审核	张海娜	201171018	图幅		mm		
核准	章妹	20181113	比例		1:1		
			图幅		A4		



: 1 1