



P. C. B LAYOUT

Material材料
 Insulator 塑胶: 30% Glass filled PBT, (UL 94V-0)
 Contact 端子: Brass 黄铜
 Electrical Characteristics 电气特性
 Current rating 额定电流: 1.5AMP
 Dielectric Withstanding Voltage 耐压:
 AC 1000V for 1Minute.
 Insulator Resistance 绝缘电阻:
 1000MΩ Min. AT DC 500V.
 Contact Resistance 接触电阻: 30MΩ Max. AT DC 100mA.
 Operating Temperature 工作温度: -40°C ~ +105°C

未注公差尺寸			KSM 9001-36321C 232		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD			
尺寸	公差				上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD			
X.	±0.3	±5°	版本号	20171018 A/0		TEL:86-21-34975176/51571121		
X.X	±0.2	±3°						
X.XX	±0.15							
绘图	周元金	201171018	图编号	ZR20171018-1				
审核	张海娜	201171018	物料编号	110654				
核准	章妹	20181113						



: 1 1