



P.C.B LAYOUT

Material材料  
 Insulator塑胶:30%Glass filled PBT, (UL 94V-0)  
 Contact 端子: Brass黄铜  
 Electrical Characteristics电气特性  
 Current rating额定电流:1.5AMP  
 Dielectric Withstanding Voltage耐压:  
 AC 1000V for 1Minute.  
 Insulator Resistance绝缘电阻:  
 1000MΩ Min. AT DC 500V.  
 Contact Resistance接触电阻:30MΩ Max. AT DC 100mA.  
 Operating Temperature工作温度:-40℃~+105℃

未注公差尺寸			KSM-9001-37321C 232		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD			
尺寸	公差				上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD			
X	长度	±0.3	角度	±5°	版本号	20171018 A/0		
X.X		±0.2		±3°				
X.XX		±0.15						
绘图	周元金	201171018		图编号	ZR20171018-8		TEL:86-21-34975176/51571121	
审核	张海娜	201171018		物料编号	110665		1:1	mm 图幅 A4
核准	章妹	20181113				: 1 1		