





A B C D E F



N=PIN数

Material 材料
 Insulator 塑胶: PBT PA9T (UL 94V-0)
 Contact 端子: Brass 黄铜
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金
 Electrical Characteristics 电气特性
 Current rating 额定电流: 2.5Amps
 Dielectric Withstanding Voltage 耐压:
 AC 500V for 1 Minute.
 Insulator Resistance 绝缘电阻: 1000MΩ Min.
 Contact Resistance 接触电阻: 20mΩ Max.
 Operating Temperature 工作温度: -40°C ~ +105°C
 Max. Processing Temp 瞬时温度:
 PBT 240° C for 6 seconds
 PA9T (260° C for 10 seconds)



P.C.B LAYOUT

未注尺寸公差			PIN1*40 2.54 L		上海洲日电子有限公司			
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD			
	长度	角度	版本编号 20171018 A/1		上海康司玛电子设备进出口有限公司			
X.	±0.3	±5°			Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD			
X.X	±0.2	±3°	图纸编号 ZR20171018-258		TEL:86-21-34975176/51571121			
X.XX	±0.15				物料编号		1:1 mm 图幅 A4	
制图	周元金	201171018	第三视角					
审核	张海娜	201171018						
核准	章妹	201171018						

A B C D E F