



ROHS

注：客户定制款，直接在原有型号后增加尾缀



PT:1.3 Max


OP:3.4±0.3

FP:4.2 Max


COM:UL1007 22AWG BLACK (黑色)

NO:UL1007 22AWG BLUE (蓝色)

注：尾部打端子，接2P的XH2.54mm端子插头



Circuit Diagram



NOTE:

- 1.Rating1:DC12V 3A
- Rating2:48V DC/125V AC/250V AC 0.1A
- 2.Operating force:130gf MAX
- 3.Electric Life:100,000
- 4.Mechanical Life:500,000
- 5.Ingress protection:IP67

⑦	Shrapnel	—	1	Brass	Plating silver	—
⑥	Contact	—	1	Ag	—	—
⑤	Sealed Circle	—	1	Silicone Rubber	—	—
④	Terminal	—	2	Brass(0.50t)	Plating silver	—
③	Plunger	—	1	POM	Black	—
②	Case	—	1	PA	Black	—
①	Cover	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS DATE

DRAWN LIUCAN 2021.11.11

CHECKED

APPROVALS

TOLERANCES ARE 30~以上 ±0.30 10~30 ±0.20 5~10 ±0.15 ~ 5 ±0.10 ANGLE UNIT: mm SCALE: 1:1 PROJ:

HRO ELECTRONICS CO.,LTD

TITLE: MICRO SWITCHS





PART NO. K9-2841L-6WBN-1HA

DRAWING NO. SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

ROHS

注：客户定制款，直接在原有型号后增加尾缀



NOTE:

- 1.Rating1:DC12V 3A
Rating2:48V DC/125V AC/250V AC 0.1A
- 2.Operating froce:130gf MAX
- 3.Electric Life:100,000
- 4.Mechanical Life:500,000
- 5.Ingress protection:IP67

⑦	Shrapnel	—	1	Brass	Plating silver	—
⑥	Contact	—	1	Ag	—	—
⑤	Sealed Circle	—	1	Silicone Rubber	—	—
④	Terminal	—	2	Brass(0.50t)	Plating silver	—
③	Plunger	—	1	POM	Black	—
②	Case	—	1	PA	Black	—
①	Cover	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD				
DRAWN	LIUCAN	2021.11.11					TITLE:	MICRO SWITCHS
APPROVALS							PART NO.	K9-2841L-6WBN-1BA
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
			10~30	±0.20				
			5~10	±0.15				
			~ 5	±0.10				
DRAWING NO.				SHEET 1 OF 1				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			