


1. 标准卡外露: 1.30mm, 标准卡长度15.00mm
2. 剪卡外露: 1.00mm, 剪卡长度14.80mm

NOTES:

- ELECTRICAL CHARACTERISTICS
 - CONTACT RESISTANCE: 100 Milliohms Max
 - INSULATION RESISTANCE: 1,000 Megohms Min.
 - VOLTAGE RATING: 125V.
 - CURRENT RATING: 0.5mA.
- MECHANICAL CHARACTERISTICS
 - OPERATION TEMPERATURE RANGE: -20°C~+60°C
 - DURABILITY: 3000 CYCLES


SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



MICRO SIM CARD

▨ PAD
▭ KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05



ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
③	Shell	—	1	SUS	Ni Plated	—
②	Terminal	—	6	Copper Alloy	Au Plated	—
①	Housing	—	1	LCP	Black	—
APPROVALS			DATE	 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2021.11.7				
CHECKED				TITLE:	SIM	
APPROVALS				PART NO.	SIM-14A	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.25		DRAWING NO.		
	5~10	±0.20				
	~ 5	±0.15				SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			