




ROHS



Recommended PCB Layout



NOTES:

- 1 INSULATION MATERIAL THERMOPLASTIC.
- 2 SHELL: SPCC, T: 0.30mm
PLATING: NICKEL
- 3 TERMINAL: COPPER ALLOY, T: 0.25mm
PLATING: GOLD/TIN PLATED.
- 4 INSERTION FORCE: 3.57Kgf MAX.
- 5 EXTRACTION FORCE: 1.02Kgf MIN.

③	Base	—	1	NYLON	Black	—
②	Terminal	—	4	Phosphor Bronze	Ag Plated	—
①	Housing	—	1	SPCC	Sn Plated	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD				
DRAWN	LIUCAN	2020/10/28						
CHECKED				TITLE: USB CONNECTOR				
APPROVALS				PART NO. U-A-24DD-W-17				
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:	
		10~30	±0.25					
		5~10	±0.20					
		~ 5	±0.15					
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.