

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A		NEW		22.9.3

NOTES1:

UL Standard

1. Rated voltage/current : 300V / 20A
2. Withstanding voltage : AC1600V/1Min.
3. Wire range : 24~12AWG

IEC Standard

1. Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	4KV	4KV	4KV
Rate voltage(V)	630V	400V	320V
Rate current(A)	32A		

2. Wire range : 0.2~4.0mm²

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 5.00mm, Poles : N=01~12P
3. Stripping length : 9~11mm
4. Operating temperature: -40°C~+105°C
5. Undimensioned tolerances:



Pitch range in mm		Nominal dimension range in mm						-	∩	□
To	Over	To	Over	To	Over	To	Over	0.1/10		
6	6 TO 10	30	30 TO 60	60	60 TO 100	100	100 TO 150			
	±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'	

6. RoHS Compliance

Ordering Information

JL245R- 500 XX G 0 1

- Pitch 500=5.0PH
- No. of pins 2P~24P
- Housing Color: B=Black, G=Green, U=Blue, R=Red, W=White, Y=Yellow, □=Orange, E=Grey
- Packing: 0=Pe bag, T=Tube, A=Tray



DRAW	SHUANGPING ZHENG	SCALE	FIT	东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	LICHAD LIU	SIZE	A4		
		SHEET	1/1		
APPROVE	YONGLIANG GAO	PROJ.		PART NO.	JL245R-500XXG01
				TITLE:	JL245R-5.0-XXP 弹簧式/弯脚/绿色