


NOTES:

1. MATERIAL:
  - 1.1.HOUSING: LCP ,COLOR IS BLUE,HIGH TEMPERATURE PLASTIC;
  - 1.2.CONTACT: BRASS ( H65 T=0.20&0.25mm);
  - 1.3.SHELL: COLD ROLLED IRON ( SPCC T=0.30mm);
2. ELECTRICAL:
  - 4.1. VOLTAGE RATING: 30V DC ;
  - 4.2. CURRENT RATING: 1.5A ;
  - 4.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
  - 4.4. WITHSTAND VOLTAGE: 100 VAC RMS 50(60)Hz,1MIN.;
  - 4.5. INSULATION RESISTANCE: 100MEGOHMS MIN @500V DC;
5. MECHANICAL:
  - 5.1. MATING FORCE: 35N MAX.;
  - 5.2. UNMATING FORCE: 5~35N ;
  - 5.3. OPERATING LIFE: 1500 CYCLES MIN.;
6. PLATING:
  - 6.1. TERMINAL:
    - NI PLATING OVER ALL,
    - Tin PLATING ON SOLDER AREA,
    - Au G/Fu" ON CONTACT AREA;
  - 6.2.SHELL: NI PLATING OVER ALL;
7. ENVIRONMENTAL:
  - 7.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
  - 7.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;



PIN NUMBER	SIGNAL NAME
PIN 1	Vbus
PIN 2	D-
PIN 3	D+
PIN 4	GND
PIN 5	StdA_SSRX-
PIN 6	StdA_SSRX+
PIN 7	GND_DRAIN
PIN 8	StdA_SSTX-
PIN 9	StdA_SSTX+
SHELL	GND

GENERAL TOLERANCE			制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
DIM	TOL		审核 CHECK		产品名称 TITLE	TYPE AF 9P 3.0 180° L11.5mm 直脚 平口	版本 REV.	A
X.X	±0.30		批准 APPROVAL		产品料号 PART NO.	HC-ST-003-02-11.5-Z	单位 UNITS	mm
X.XX	±0.20		比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
X.XXX	±0.10		投影 Projection					
Angle	±3.0°							

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE
1	初版发行	