


未注公差/General tolerances(mm)													
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	
~3	~6	~10	~18	~30	~50	~80	~120	~180	~250	~315	~400	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50
												0.1/10	
												±2'	

A


A




3.30      3.50x(N/2-1)+3.90      3.30

B

B



15.00  
18.50 Ref.  
7.80




C

C

3.50  
3.50x(N/2-1)      1.95

D

D



2.50  
6.25

6	Screw	Steel	Zn Plated
5	Clamp	Copper alloy	Sn Plated
4	Spring	Stainless steel	/
3	Button	PA66-GF	UL94V-0
2	Cover	PA66-GF	UL94V-0
1	Housing	PA66-GF	UL94V-0
ITEM	PART NAME	MATERIAL	NOTES

UL 标准/UL Standard:	B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)	300/10	50/10	300/10
EC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree	III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)	160/13.4	160/13.4	320/13.4
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	2.5	2.5	2.5
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm <sup>2</sup> /AWG)	0.2~1.5/28~16		
间距/Pitch(mm)/线数范围/Poles	3.50/N=04~48P		
剥线长度/Stripping length(mm)	10-11		
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		

MATERIAL: /	SURFACE: /		
MAT NO.: /	宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD		
STATUS: /			
APPD: Li GL 2020.06.04			
CHKD: Ma EK 2020.06.04			
DRFT: Lee 2017.03.30	NAME: 15EDGKNHBM-3.5-XXP-1Y-00A(H)		REV: D0-4
DRAWING NO.: 15EDGKNHBM-3.5-C01		TYPE: CUSTOMER DRAWING	SCALE: 2:1 SHEET 1/1

REV	ECN	DESCRIPTION	DRFT	DATE
1				
2				
3				
4				
5				
6				