


PCBLayout(Pattern Side)



Color	VR	IF	Recommended Operating	IF	
				Nom	Max
White	DC5V	20mA	20mA	3.0V	3.6V
Red	DC5V	20mA	20mA	1.7V	2.4V
Yellow	DC5V	20mA	20mA	1.9V	2.4V
Blue	DC5V	20mA	20mA	3.0V	3.6V
Green	DC5V	20mA	20mA	1.9V	2.4V

LED colour(LED颜色)	Part No. 料号
White(白色)	K6-6136D-□□-01
Red(红色)	K6-6136D-□□-02
Blue(蓝色)	K6-6136D-□□-03
Green(绿色)	K6-6136D-□□-04
Yellow(黄色)	K6-6136D-□□-05
Yellow/White(黄色/白色)	K6-6136D-□□-15

NO.	Operating Type	Part No.
1	Push To Lock (自锁)	K6-6136D-L1-□□
2	Push No Lock (无锁)	K6-6136D-N1-□□

②	Terminal	—	3	Phosphor bronze	Au Plating	—
①	Housing	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/11/11				
CHECKED				TITLE:	LED Tact Switch	
APPROVALS				PART NO.	K6-6136D-□□-□□	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10	±2'	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			