



技术参数:

- 插芯:
- 插针数: 1
  - 额定电流: 200A
  - 额定电压: 1000V
  - 额定脉冲电压: 8kV
  - 污染等级: 3
  - 依据UL的额定电压: 600V
  - 绝缘阻抗:  $>10^{10}\Omega$
  - 材料: 聚碳酸酯
  - 颜色: RAL 7032 (浅灰色)
  - 温度范围:  $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
  - 依据UL 94的阻燃等级: V0
  - 可插拔次数:  $>500$
- 插针:
- 接线方式: 轴向螺栓连接
  - 材料: 铜合金
  - 表面处理: 镀银
  - 接触电阻:  $<0.2\text{m}\Omega$
  - 线径范围:  $40-70\text{mm}^2$
  - 内六角扳手: SW-5\*150
  - 剥线长度: 16mm
  - 拧紧力矩:
    - $\text{mm}^2$ : 25 35 50 70
    - N·m: 8 8 9 10

Technical specification:

- Insters:
- No. of contact: 2
  - Rated current: 200A
  - Rated voltage: 1000V
  - Rated impulse voltage: 8kV
  - Pollution degree: 3
  - Rated voltage acc.to UL: 600V
  - Insulation resistance:  $>10^{10}\Omega$
  - Material: polycarbonate
  - Colour: RAL 7032(light grey)
  - Temperature range:  $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
  - Flammability acc.to UL 94: V0
  - Mating cycles:  $>500$
- Contacts:
- Terminal: axial screw terminal
  - Material: copper alloy
  - Surface: hard-silver plated
  - Contact resistance:  $<0.2\text{m}\Omega$
  - Wire gauge:  $40-70\text{mm}^2$
  - Hexagonal driver: SW-5\*150
  - Stripping length: 16mm
  - Tightening torque:
    - $\text{mm}^2$ : 25 35 50 70
    - N·m: 8 8 9 10

						表面处理 Finish		-		图号 Drawing No.		-		
						材料 Material		-		产品代号 Part Code		H2MKPE-001.2-F		
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date					产品料号 Part No.		1290010210002	
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name		-		
绘图 Drawn	BQ LUO	18.10.2010	标准化 Stand.	-	-	1:1	V1.0	92.5g	-					
审核 Checked	P RAO	18.10.2010												
工艺 Process	-	-	批准 Approved	YY LIN	18.10.2010	All Dimensions in mm Original Size DIN A 4				厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD				