



H=XXmm

				TOLERANCE公差							
				UNLESS SPECIFIED							
7	STEEL BALL 钢球	STEEL 钢	2		UP TO 5mm: ±0.1	ANGULAR	1				
6	SPRING 弹簧	SU 不锈钢	1		ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS 修订版		BY APPD
5	CONTACT 接触片	PBS 磷铜	2	Ag-PLATED 镀银			TITLE: VERTICAL SLIDE SWITCH 垂直滑动开关		UNIT : MM	ROHS COMPLIANT	DWN
4	TERMINAL 端子	BRASS 黄铜	14	Ag-PLATED 镀银			MODEL: SS26D01 PA66柄		SCALE: 1:1	CHK'D	
3	BASE 底座	PHENOLIC RESIN 电木板	1	BLACK 黑色			深圳市金航标电子有限公司		www.kinghelm.com.cn		APPD
2	FRAME 外壳	Iron 铁	1	Ni-PLATED 镀镍			KH-SS26D01-G6		0755-28190160		PRO.AGL: REV :A0
1	KNOB 胶柄	PA66	1	BLACK 黑色							
NO.	PART NAME 零件名称	MATERIAL 原料	QTY 数量								