



SCHEMATIC

PCB LAYOUT

- | | |
|---------------------------------------|--|
| 1.Limit value: 0.3A 50V DC | 5.动作力: 260±100gf |
| 1.额定值: 0.3A 50V DC | 6.Stroke: 2.0mm |
| 2.Contact resistance: ≤ 100m Ω Max | 6.行程: 2.0mm |
| 2.接触电阻: ≤100mΩ MAX | 7.Service life: 10000 times |
| 3.Insulation resistance: ≥ 100m Ω Max | 7.使用寿命: 10000次 |
| 3.绝缘电阻: ≥100mΩ MAX | 8.Service temperature: - 16 °C ~ + 60 °C |
| 4.Withstand voltage: AC 500V 1 min | 8.使用温度: - 16°C ~ + 60°C |
| 4.耐电压: AC 500V 1 min | 9.Contact type: 1P3T |
| 5.Action force: 260 ± 100gf | 9.接触型式: 1P3T |

4	Terminal 端子	Brass 黄铜	4	Ag plated 镀银
3	Base 基座	Phenolic Resin 酚醛树脂	1	
2	Frame 框架	SUS	1	Natural
1	Hand shank 手柄	PA66	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4					COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: SK-13D07-4	
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1						ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION			ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				