



P . C . B LAYOUT

- 规格 Specifications:
- 额定电压 Voltage rating: 250VAC/DC。
 - 额定电流 Current rating: 2A AC/DC
 - 耐电压 Withstanding voltage: 500V AC/minute
 - 温度区间 Temperature range: -40°C to +105°C
 - 绝缘电阻 Insulation resistance: ≥1000MΩ Min
 - 接触电阻 Contact resistance: ≤20MΩ Max
 - 材料 Material: PA6T UL94V-0
 - 镀层 Plating Category: 1U"Gold
 - 回流焊温度 Reflow soldering temperature: 260±5°C, 10s

X4621 W V S - 2xXX I - C80 D64
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No.
2. Category: W-Water
3. Welding Board Angle: V-Stright 180°
4. Welding Way S-SMT
5. Row No -Pin No: 2xXX-2x02P-2xXXP
6. Plastic height: I=2.0mm
7. Plastic length: C=8.0mm
8. Plastic length: D=6.4mm

X4621WVS-2xXXI-C80D64	PA6T UL94V-0	Brass	1U"Gold	X4621F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.0mm BTB Style Connector
DWN	VIEW:	PART NO.: X4621WVS-2xXXI-C80D64
CHKD	UNIT: mm/in	DWG NO.: X-X4621WVS-2xXXI-C80D64
APPD	SIZE: A4	

ΔX					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

