



REV.	ECN NO.	REVISED	DATE

NOTE:


1.MATERIAL:

- a.HOUSING:PP BLACK
- b.SPRING:MUSIC WIRE
(SURFACE PLATING: NI100u"~120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL
- b.OPERATING TEMPERATURE: -40° C~ +80° C



ORDERING INFORMATION BH-AA-B1AJ018-140

电池盒
电池型号
SMT 180° TYPE

线长 (MM)
PLATING:
A-Au1U"
J-Ni100U"~120U"
K-Sn100U"~120U"

MATERIAL:
1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

工程部
2021-02-01
H. WANG

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2021-02-01
WEIGHT:		CHKD ZhouRuicai	DATE 2021-02-01
SHEET 1 OF 1		APVD XueShunyong	DATE 2021-02-01
SCALE:		SIZE: A4	VIEW:
UNIT: mm		REV.: A/1	OBJECT: MY
TITLE: 电池盒BH-AA-4J双面靠背 (22#线长140mm带3P2.0正向插头)		PART NO.: BH-AA-B1AJ018-140	
DRAW NO.:WD-CP-0130			

2	SPRING	4	MUSIC WIRE	NI-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR