


修改 REV NO	标记 MARK	修改描述 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		新增 DWG		2016-03-12

- 1.Material**
- 1.1: Housing: PA46 UL94-V0 Color:Nature.
 - 1.2: Contact: C5191-H T=0.20±0.01.
 - 1.3: LEG: C2680-H T=0.25±0.01.
- 2.Plating**
- 2.1: Contact: Gold flash over Nickel.
 - 2.2: LEG: Gold flash over Nickel.
- 3.Rating:**
- 3.1: Operating Voltage: 50V AC/DC.
 - 3.2: Current Rating: 0.5A AC/DC.
 - 3.3: Operating Temperature:-40°C~+80°C.
- 4.Mark** * is the important dimension
- 5.Pater Number:**



PORT NO	Dimension			PORT NO	Dimension		
	A	B	D		A	B	D
04P	4.10	3.25	2.60	25P	14.60	13.75	13.10
05P	4.60	3.75	3.10	26P	15.10	14.25	13.60
06P	5.10	4.25	3.60	27P	15.60	14.75	14.10
07P	5.60	4.75	4.10	28P	16.10	15.25	14.60
08P	6.10	5.25	4.60	29P	16.60	15.75	15.10
09P	6.60	5.75	5.10	30P	17.10	16.25	15.60
10P	7.10	6.25	5.60	31P	17.60	16.75	16.10
11P	7.60	6.75	6.10	32P	18.10	17.25	16.60
12P	8.10	7.25	6.60	33P	18.60	17.75	17.10
13P	8.60	7.75	7.10	34P	19.10	18.25	17.60
14P	9.10	8.25	7.60	35P	19.60	18.75	18.10
15P	9.60	8.75	8.10	36P	20.10	19.25	18.60
16P	10.10	9.25	8.60	37P	20.60	19.75	19.10
17P	10.60	9.75	9.10	38P	21.10	20.25	19.60
18P	11.10	10.25	9.60	39P	21.60	20.75	20.10
19P	11.60	10.75	10.10	40P	22.10	21.25	20.60
20P	12.10	11.25	10.60	41P	22.60	21.75	21.10
21P	12.60	11.75	11.10	42P	23.10	22.25	21.60
22P	13.10	12.25	11.60	43P	23.60	22.75	22.10
23P	13.60	12.75	12.10	44P	24.10	23.25	22.60
24P	14.10	13.25	12.60	45P	24.60	23.75	23.10

HFC 深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co., LTD
 电话: 0755-23304126 传真: 0755-29940187

TITLE: 产品名称: FPC 0.5间距1.2高无镀双面接
 PART NO: 产品编号: 0.5K-1.2W-nPWB

UNLESS OTHERWISE SPECIFIED 公差参数表	APPR: 核准: 王建业	SCALE: 1:1	UNIT: mm	CODE NUMBER: A001
X.X ±0.30	X.X' ±3°	DATE: 2016-03-12		
X.XX ±0.20	X.XX' ±2°	SCALE: 1:1		
X.XXX ±0.10	X.XXX' ±1°	UNIT: mm		

Recommend P.C.B Layout

