


4805 (3/11)

		2					1			
	LOC DIST			REVISIONS						
	GΡ	00	Р	LTR		DESCRIPTION		DATE	DWN	APVD
•				А	REVISED PER	ECO-15-000199		13JAN2015	ΑP	DG
				В	REVISED PER	ECO-17-008190		03MAR2017	JΥ	SH
				С	REVISED PER	ECO-17-013690		04AUG2017	JΥ	SH

	8	Ø1.80	2227580-3			
	7	Ø1.60	2227580-2			
	4	Ø1.80	2227580-1			
	SCREW Application	DIAMETER A OF HOLE	P A R T N U M B E R	ļ		
A CONTROLLED DOCUMENT. R. TREA CHK R. HENR	13DEC2012	STE T	E Connectivity			
$\begin{array}{c c} & \text{TOLLRANCES UNLESS} \\ & \text{OTHERWISE SPECIFIED:} \\ \hline \\ 0 & \text{PLC} \\ \hline \\ 1 & \text{PLC} \\ 2 & \text{PLC} \\ 2 & \text{PLC} \\ 3 & \text{PLC} \\ \end{array}$	- NAME	RECEPTACLE ASSEMBLY, 1X1, RIGHT ANGLE, INTERNAL MINI SAS HD				
4 PLC ±- ANGLES ±- FINISH - WEIGHT	32101 SIZE CAG	e code drawing no - C=2227580	RESTRICTED TO			
CUSTOME	R DRAWING	scale 8:1	sheet of 2 rev C			




6


4805 (3/11)

8

7







THIS DRAWING IS A DIMENSIONS: mm

	2			1			
LOC G P	D I S T	Ρ	LTR	REVISIONS DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	_

DETAIL W SCALE 20:1

CONTROLLED DOCUMENT.	DWN 13DEC2012 R.TREA снк 13DEC2012 R.HENRY	TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±-	APVD - PRODUCT SPEC 108-32038 APPLICATION SPEC	RECEPTACLE ASSEMBLY, 1X1, RIGHT ANGLE, INTERNAL MINI SAS HD				
4 PLC ±- ANGLES ±- FINISH -	114-32101 WEIGHT _	SIZE CAGE CODE DRAWING NO A 1 - C=2227580 -				
-	CUSTOMER DRAWING	SCALE 8.1 SHEET 2 OF 2 REV C				

В

D

С