

- NOTES:
SPECIFICATION:
1. CURRENT RATING: 5.0A MAX
 2. VOLTAGE: 100 VAC
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C
 4. CONTACT RESISTANCE: 40 MILLIONHM MAX
 5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
 6. LNSERTION FORCE : 5N~20N
 7. UNMATING FORCE: 8N~20N
 8. DURABILITY: 10,000 CYCLES

USB TYPE-C PIN ASSIGNMENTS

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXP1	B11	SSRX1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRX1	B2	SSTXP2
A12	GND	B1	GND

P/N	(L)	COLOR	额定电流
HC-TYPE C-24P-CP0.8-5A-L10.45-01	10.45mm	黑色	5A

Ordering Information



HC-TYPE C - 24P - * * * - * A - L * - * - 01

#P	Type	Mount	Current	Length	Color
24P	Pin-Top	Mount (SMT)	3A	10.45mm	Black
24P	Pin-Top	Mount (SMT)	5A	10.45mm	Black
24P	Pin-Top	Mount (SMT)	5A	10.45mm	White
24P	Pin-Top	Mount (SMT)	5A	10.45mm	Blue
24P	Pin-Top	Mount (SMT)	5A	10.45mm	Green
24P	Pin-Top	Mount (SMT)	5A	10.45mm	Orange
24P	Pin-Top	Mount (SMT)	5A	10.45mm	Yellow


			GENERAL TOLERANCE	制图	深圳市华灿天禄电子有限公司			
			DIM TOL	DRAWING	ShenzhenhuacantianluELECTRONICS CO.,LTD			
			X.X ±0.30	CHECK	产品名称	TYPE C F 24P 夹板式0.8	版本	A
			X.XX ±0.20	APPROVAL	TITLE	L10.45mm 无弹无柱	REV.	
			X.XXX ±0.10	SCALE	产品料号	HC-TYPE-C-24P-CP0.8-5A-L10.45-01	UNIT	mm
序号	变更内容	日期	Angle ±3.0°	投影	PART NO.		UNITS	
No.	MODIFY CONTENT	MODIFY DATE		Projection	MATERIAL		SHEET	1/2
1	初版发行							

pcs/box	boxes/Carton	Pcs/Box
50	240	12000

50PCS PRODUCTS PER TUBE





TUBE



标签

CARTON



			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM	TOL	审核 CHECK	产品名称 TITLE	TYPE C F 24P 夹板式0.8 L10.45mm 无弹无柱-包装图	版本 REV.	A
			X.X	±0.30	批准 APPROVAL	产品料号 PART NO.	HC-TYPE C-24P-CP0.8-5A-L10.45-01	单位 UNITS	mm
1	初版发行		X.XX	±0.20	比例 SCALE			页次 SHEET	2/2
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection	材料 MATERIAL			
			Angle	±3.0°					