




注：本板为禁止运输、复制、编辑文件，以及用其内容进行交流

REV	ECN NO.	CONTENT	CHK	DATE



NOTES1:
UL Standard
1.Rating voltage/current: 300V//10A
2.withstanding voltage: AC2500V//1Min
3.Wire range: 20~16AWG
IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	II	II
Rate Impulse Voltage(KV)	/	4	/
Rate Voltage(V)	/	320V	/
Rate Current(A)	/	10A	/

2. wire range: 0.5-1.5mm²

NOTES2:
1.Housing: PA66(UL94V-0)
2.Solder Pin: Copper alloy(rSn Plated)
3.Button: PA66(UL94V-0)
4.Cover: PA66(UL94V-0)
5.Spring: Stainless Steel

NOTES3:

1.Pitch: 5.0mm Poles: 02-24P
2.Stripping length: 9-10mm
3.Operating temperature: -40℃~+105℃
4.RoHS Compliance

How to order

MX235 - 5.0 - XXP - XXXX - XX - X - X - X
产品型号 间距 颜色: 极数
颜色: 01:带刷颜色
灰色:GY 橙色:OE 02-99:
蓝色:BU 红色:RD 定制颜色
黑色:BK 透明色:TT
绿色:GN 黄色:YW
透明色:TT 白色:WE

A-Z其他定制
0:Y一字螺丝
1:S十字螺丝
2:P:平头十字螺丝
Cu:铜
Fe:铁

Pitch	Range	In mm	Nominal Dimension	Range		
mm	Over	In	Over	Over	Over	Over
	6	10	30	60	100	150
TO	TO	TO	TO	TO	TO	TO
6	10	24	30	60	100	150
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00
					±1.00	±1.30
						±2°

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	UNITS	MM	SHEET/OF
APP	DATE	SCALE	1:1	A4	1/1
	DATE	NAME	MX235-5.0-XXP		
		DWGNO.			



CXI MAIXU ELECTRONICS CO., LTD.
慈溪市迈旭电子有限公司