BUZZERS

⊗TDK

(1/1)


Lead wire type PS15

PS1550L40N

FEATURES

- Miniature size(ø15×T0.95mm).
- O High cost performance.
- \bigcirc The installation of this type is easy with both-sided tape.
- O This product adopts an excellent both-sided adhesive tape in bonding and the sound characteristic.

SHAPE & DIMENSIONS





SPECIFICATIONS

Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	20Vo-P max. [without DC bias]
Minimum delivery unit	12000 pieces

FREQUENCY SOUND PRESSURE CHARACTERISTICS

SINE WAVE DRIVE





* The frequency characteristic changes depending on the case shape and the installation method.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.