


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	07NOV2008	MM	AO
	B	REVISED	29JAN2020	RI	EI


CIRCUIT NO CAVITY MARK

$3.5 \times n = A$




1. MATERIAL: GLASS FILLED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。




11.3 1.2

SERIES CODE




COMPANY LOGO

15




ROW ID


KEYING MARK



3POS(X-KEY): 1-2040444-1



6POS(X-KEY): 1-2040444-2



9POS(X-KEY): 1-2040444-3

12	X	3	10.5	15.5	14.3	1-2040444-4
9	X	2	7.0	12.0	10.8	1-2040444-3
6	X	1	3.5	8.5	7.3	1-2040444-2
3	X	-	-	5.0	3.2	1-2040444-1
POS	KEY	n	A	C	D	PART NO

AS SHOWN 12POS(X-KEY) : 1-2040444-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 07NOV2008	TE Connectivity	
DIMENSIONS: 単位: 耗 mm		CHK T. SAKAMOTO 07NOV2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5°		APVD A. OISHI 07NOV2008	NAME 名称 DYNAMIC D1500T 3.5mm PITCH TAB HSG (FREE HANGING TYPE) 6-12POS	
0-PLC ± 1-PLC ±0.1 2-PLC ±0.02 3-PLC ±0.005 4-PLC ±0.0005 ANGLES ±		PRODUCT SPEC 製品規格 108-78268, 78298	DRAWING NO 番号	
MATERIAL 材料		APPLICATION SPEC 取付適用規格 114-5377	SIZE A3	CAGE CODE 00779
FINISH 仕上		WEIGHT -	DRAWING NO 番号 C-2040444	
		CUSTOMER DRAWING	SCALE 尺度 2:1	SHEET 1 OF 1
			RESTRICTED TO REV B	